

TECHNICAL DATA SHEET

DESCRIPTION

Dayton Superior's Individual High Chair is used to support upper steel directly or by means of a carrier bar. Available in 2" to 15" heights in bright basic, plastic protected, epoxy-coated, or galvanized wire.

APPLICATION

To support reinforcing bar or wire mesh during concrete placement in Flat Slab, Tilt Wall Panel, Elevated Slabs, Precast Panels projects, to maintain proper concrete coverage.

PRODUCT SPECIFICATION


- Cover Height: Available in heights of 2" to 15" in increments of 1/4". Chairs over 12" require cross bracing or lacing of legs.



**High Chair w/
turned up leg**



**Stainless dowels
on chairs over 3"**



**Plastic tipped
legs available**



**Plastic dipped
legs available**

FEATURES

- Forming cradle for placing reinforcing bar.
- Designed to resist deformation under construction loading.
- Wide leg span to allow chair to straddle lower bars.
- Foot designed for use on multiple forming surfaces. Plastic Dipped and Plastic Tipped chairs designed for exposed conditions, i.e. Tilt Wall Panels.

ORDERING INFORMATION

INDIVIDUAL HIGH CHAIR - PLAIN

Product Code	Description	Weight
73100	2"	0.148 LB
73120	2-1/2"	0.166 LB
73140	3"	0.193 LB
73160	3-1/2"	0.220 LB
73180	4"	0.245 LB
73190	4-1/4"	0.258 LB
73200	4-1/2"	0.280 LB
73210	4-3/4"	0.289 LB
73220	5"	0.320 LB
73260	6"	0.492 LB
73280	6-1/2"	0.507 LB
73340	8"	0.620 LB
73380	9"	0.682 LB
72710	9-1/2"	0.960 LB
72730	10"	0.990 LB
72770	11"	1.080 LB
72810	12"	1.200 LB

INDIVIDUAL HIGH CHAIR - PLASTIC TIPPED

Product Code	Description	Weight
73106	2"	0.150 LB
73126	2-1/2"	0.170 LB
73146	3"	0.190 LB
73186	4"	0.240 LB
73226	5"	0.310 LB
73236	5-1/4"	0.396 LB
73246	5-1/2"	0.409 LB
73256	5-3/4"	0.414 LB
73266	6"	0.449 LB
73276	6-1/4"	0.470 LB
73286	6-1/2"	0.484 LB
73296	6-3/4"	0.492 LB
73306	7"	0.510 LB
73316	7-1/4"	0.538 LB
73326	7-1/2"	0.540 LB
73336	7-3/4"	0.550 LB
73346	8"	0.579 LB
73356	8-1/4"	0.630 LB
73366	8-1/2"	0.660 LB
73376	8-3/4"	0.660 LB
73386	9"	0.660 LB
72706	9-1/4"	0.886 LB
72716	9-1/2"	0.950 LB
72726	9-3/4"	0.974 LB
72736	10"	1.025 LB
72746	10-1/4"	1.050 LB
72756	10-1/2"	1.070 LB
72766	10-3/4"	1.070 LB
72776	11"	1.122 LB
72786	11-1/4"	1.120 LB
72796	11-1/2"	1.123 LB
72806	11-3/4"	1.130 LB
72816	12"	1.200 LB

TECHNICAL DATA SHEET

INDIVIDUAL HIGH CHAIR - GALVANIZED & PLASTIC TIPPED

Product Code	Description	Weight
73108	2"	0.154 LB
73149	3"	0.194 LB

INDIVIDUAL HIGH CHAIR - PLASTIC DIPPED

Product Code	Description	Weight
73103	2"	0.161 LB
73123	2-1/2"	0.180 LB
73133	2-3/4"	0.200 LB
73143	3"	0.213 LB
73163	3-1/2"	0.242 LB
73173	3-3/4"	0.257 LB
73183	4"	0.261 LB
73193	4-1/4"	0.279 LB
73203	4-1/2"	0.290 LB
73213	4-3/4"	0.302 LB
73223	5"	0.360 LB
73243	5-1/2"	0.450 LB
73253	5-3/4"	0.474 LB
73263	6"	0.497 LB
73273	6-1/4"	0.510 LB
73283	6-1/2"	0.530 LB
73293	6-3/4"	0.540 LB
73303	7"	0.570 LB
73313	7-1/4"	0.600 LB
73323	7-1/2"	0.610 LB
73333	7-3/4"	0.640 LB
73343	8"	0.640 LB
73353	8-1/4"	0.650 LB
73363	8-1/2"	0.670 LB
73373	8-3/4"	0.670 LB
73383	9"	0.680 LB
72713	9-1/2"	1.020 LB
72733	10"	1.000 LB

INDIVIDUAL HIGH CHAIR - EPOXY COATED

Product Code	Description	Weight
73107	2"	0.170 LB
73127	2-1/2"	0.180 LB
73147	3"	0.197 LB
73157	3-1/4"	0.218 LB
73167	3-1/2"	0.230 LB
73177	3-1/4"	0.250 LB
73187	4"	0.253 LB
73197	4-1/4"	0.274 LB
73207	4-1/2"	0.279 LB
73217	4-3/4"	0.296 LB
73227	5"	0.330 LB
73237	5-1/4"	0.440 LB
73247	5-1/2"	0.460 LB
73257	5-3/4"	0.469 LB
73267	6"	0.501 LB
73287	6-1/2"	0.530 LB
73307	7"	0.558 LB
73327	7-1/2"	0.594 LB
73347	8"	0.620 LB
72747	10-1/4"	1.070 LB

MANUFACTURER

Dayton Superior Corporation
 1125 Byers Road
 Miamisburg, OH 45342
 Customer Service: 888-977-9600
 Technical Services: 877-266-7732
 Website: www.daytonsuperior.com

WARRANTY (ACCESSORIES)

Limited Warranty. Dayton warrants, for a period of 60 days from the date of shipment (three years from the date of shipment in the case of formwork, excluding any consumable Products included with such formwork), that Products and any associated application drawings and engineering services provided by Dayton ("Ancillary Services") will be free from defects in material and workmanship and, in the case of custom designed formwork, that the formwork will meet the specifications set forth in the design drawings approved by Dayton and Customer. Any claim under this warranty must be made in writing within such warranty period. If any Product and/or Ancillary Service covered by a timely claim are found to be defective, Dayton will, within a reasonable time, make any necessary repairs or corrections or, at Dayton's option, replace the Product. Unless pre-authorized by Dayton in writing, Dayton will not accept any charges for correcting defects or accept the return of any Product. This warranty will not apply to any Products that have been subjected to misuse, neglect, storage damage, misapplication, accident or any other damage caused by any person other than Dayton, or that have not been maintained in accordance with Dayton's specifications. THIS LIMITED WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES AS TO THE PRODUCTS AND ANCILLARY SERVICES. DAYTON MAKES NO OTHER WARRANTIES OR GUARANTEES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OTHERWISE. THE REMEDIES SET FORTH IN THIS SECTION ARE CUSTOMER'S EXCLUSIVE REMEDY FOR BREACH OF WARRANTY.